



Quality Wood Finishing Products®

EasyGlaze

#9000

For Classic Glaze Effects. PreCat or Conversion Varnish System

Woodwright's Easy Glaze contains No HAPS and Ultra Low VOC. With a very workable formulation, this product allows for much easier standard highlight glazing and wash-over techniques. Enjoy the low odor of Easy Glaze! Easy Glaze is available in any solid color. You can feel confident applying Easy Glaze under any Woodwright Conversion or Precatalyzed Varnish. Very easy wiping, simple to use. Come to The Woodwright School to learn these techniques. Call for a class schedule.

DIRECTIONS FOR USE

Use with Solid Color Varnish (Paint):

1. Apply primer or 1st color coat. Allow to dry completely. Sand as usual.
2. Apply solid color varnish or 2nd color coat. Allow to dry completely. Do not sand until you are ready to glaze.
3. When you are ready to glaze, sand surface with 320 or 400 grit sandpaper.
4. Apply glaze as desired. (When applying over whites or pastels glaze will change the overall color of your piece. To reduce this effect wipe over the surface with a cloth dampened with mineral spirits after applying glaze.)
5. Allow to dry for 1 hour and not more than 2 hours.
6. Apply clear sealer. Let dry. Sand.
7. Apply topcoat.

Use with Stain:

1. Apply stain, as usual. Allow to dry.
2. Apply clear sealer. Allow to dry. Do not sand until you are ready to glaze.
3. When you are ready to glaze, sand with 320 or 400 grit sandpaper.
4. Apply glaze as desired. Allow to dry for 1 hour and not more than 2 hours.
5. Apply 2nd coat of clear sealer. Allow to dry. Sand, as usual.
6. Apply topcoat.



1225-C US Route 62 · Wilmot, Ohio 44689 · 800.322.8172 · WoodwrightFinish.com